Product Data Sheet FilmTec™ Fortilife™ Nanofiltration Membranes



FilmTec[™] Fortilife[™] NF1000 HP

Salt-Selective Nanofiltration Membrane Element for Water and Waste Reclamation

Key Features

- High monovalent-divalent ion selectivity to enable the production of high purity salt solutions while reducing liquid volume to downstream thermal treatment.
- Improved efficiency over FilmTec[™] Fortilife[™] NF1000 when operating above 400 psi.
- Expertly designed and optimized membrane chemistry to enable a reliable and robust element lifetime.
- High productivity membrane allows for increased water and resource recovery and/or reduced energy consumption.

Key Applications

- Industrial Minimum- and Zero-Liquid Discharge (MLD/ZLD).
- Industrial resource recovery and recycling, such as in textiles, steel & metals, chemical & petrochemical.
- Softening.
- Chloralkali processing.
- Landfill leachate (de-coloring).

Typical Properties


	Permeate Flow				
	Active Area	Feed Spacer Thickness	Rate	Stabilized Salt Rejection	Minimum Salt Rejection
FilmTec™ Element	ft ² (m ²)	(mil)	gpd (m ³ /d)	(%)	(%)
Fortilife™ NF1000 HP	400 (37)	34	8,200 (31)	99.2	98.0

1. Permeate flow and salt rejection based on the following standard conditions: 2,000 ppm MgSO4, 70 psi (4.8 bar), 77°F (25°C), and 15% recovery.

2. Flow rates for individual elements may vary but will be no more than 15% below the value shown.

3. Sales specifications may vary as design revisions take place.

Element Dimensions





FilmTec™ supplies coupler part number 313198 with each element. Each coupler includes two 3-912 EPR O-rings (part number 151705).

FilmTec™ Element Fortilife™ NF1000 HP Dimensions – inches			
А	40.0 (1,016)		
В	1.125 ID (29)		
С	7.9 (201)		

1. For element weight information refer to What is the weight of FilmTec[™] elements as delivered?

2. For element packaging and shipping information refer to How are FilmTec™ elements packaged and shipped?

Suggested Operating Conditions

Membrane Type	Polypiperazine Thin-Film Composite		
Maximum Operating Temperature ¹	113°F (45°C)		
Maximum Operating Pressure	1,200 psig (83 bar)		
Maximum Pressure Drop			
Per Element	15 psig (1.0 bar)		
Per Pressure Vessel (Minimum 4 Elements)	50 psig (3.5 bar)		
pH Range			
Continuous Operation ¹	3-10		
Short-Term Cleaning (30 min.) ²	1-12		
Maximum Feed Flow ³	75 gpm (17 m ³ /hr)		
Maximum Feed Silt Density Index	SDI 5		
Free Chlorine Tolerance ⁴	< 0.1 ppm		

- Maximum temperature for continuous operation above pH 10 is 95°F (35°C).
- Refer to <u>FilmTec[™] Cleaning</u> <u>Guidelines</u> (Form No. 45-D01696-en).
- For recommended feed and permeate flow rates, flux, and recovery for various feed sources, refer to <u>FilmTec™ Design</u> <u>Guidelines for multiple-element systems of 8-inch elements</u> (Form No. 45-D01695-en).
- 4. Oxidation damage is not covered under warranty, DuPont recommends removing residual free chlorine by pretreatment prior to membrane exposure. Please refer to <u>Dechlorinating</u> <u>Feedwater</u> (Form No. 45-D01569-en) for more_information.

General Information

- Keep elements moist at all times after initial wetting.
- I For successful operation of Reverse Osmosis (RO) and Nanofiltration (NF) membrane systems, the operation must follow the guidelines provided in the <u>FilmTec™ Reverse</u> <u>Osmosis / Nanofiltration Elements Operation Excellence and</u> <u>Limiting Conditions Tech Fact</u> (Form No. 45-D04388-en).
- To prevent biological growth during prolonged system shutdowns, it is recommended that membrane elements be immersed in a preservative solution.
- The customer is fully responsible for the effects of incompatible chemicals and lubricants on elements.
- Avoid static permeate-side backpressure at all times.
- Permeate obtained from the first hour of operation should be discarded.
- The use of this product in and of itself does not necessarily guarantee the removal of cysts and pathogens from water.
 Effective cyst and pathogen reduction is dependent on the complete system design and on the operation and maintenance of the system.

Important Information

Please consider good operating practices for the optimal performance of the Reverse Osmosis membrane elements to assure damage free operation:

- 1. <u>Loading of Pressure Vessels Preparation & Element</u> <u>Loading (Form No. 45-D01602-en)</u>
- System Operation, including plant <u>Start-Up Sequence</u> (Form No. 45-D01609-en) and <u>RO & NF Systems</u> <u>Shutdown</u> (Form No. 45-D01613-en)
- 3. <u>Handling, Preservation, and Storage</u> (Form No. 45-D03716-en)

Full information of plant design, system operation, and troubleshooting is given in the <u>FilmTec™ Reverse Osmosis</u> <u>Membranes Technical Manual</u> (Form No. 45-D01504-en).

Regulatory Note

This product may be subject to drinking water application restrictions in some countries; please check the application status before use and sale.





All information set forth herein is for informational purposes only. This information is general information and may differ from that based on actual conditions. Customer is responsible for determining whether products and the information in this document are appropriate for Customer's use and for ensuring that Customer's workplace and disposal practices are in compliance with applicable laws and other government enactments. The product shown in this literature may not be available for sale and/or available in all geographies where DuPont is represented. The claims made may not have been approved for use in all countries. Please note that physical properties may vary depending on certain conditions and while operating conditions stated in this document are intended to lengthen product lifespan and/or improve product performance, it will ultimately depend on actual circumstances and is in o event a guarantee of achieving any specific results. DuPont as sumes no obligation or liability for the information in this document. References to "DuPont" or the "Company" mean the DuPont legal entity selling the products to Customer unless otherwise expressly noted. NO WARRANTIES ARE GIVEN; ALL IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE ARE EXPRESSLY EXCLUDED. No freedom from infringement of any patent or trademark owned by DuPont or others is to be inferred.